

# Custom Measurement Form for Compression Arm Sleeves & Accessories



Scan for How to Measure Videos

## Account Information (Please Print)

|                 |                       |             |       |             |               |
|-----------------|-----------------------|-------------|-------|-------------|---------------|
| Account Number  | Date Ordered          | Phone       | Fax   | Patient ID  | Date Measured |
| Account Name    | Contact               | Measured by | Title | P.O. Number |               |
| Ship to Address | Prescribing Physician |             |       | Re-order #  |               |

## Order Information

Quantity: \_\_\_\_\_ Piece(s) ☐ Left ☐ Right

### Circular Knit

|                                                    | 18-21 mmHg                      | 23-32 mmHg                      | 34-46 mmHg                      |
|----------------------------------------------------|---------------------------------|---------------------------------|---------------------------------|
| <input type="checkbox"/> Juzo Soft (with silicone) | <input type="checkbox"/> 2001   | <input type="checkbox"/> 2002   |                                 |
| <input type="checkbox"/> Juzo Dynamic              | <input type="checkbox"/> 3511   | <input type="checkbox"/> 3512   | <input type="checkbox"/> 3513   |
| <input type="checkbox"/> Juzo Dynamic Silver       | <input type="checkbox"/> 3561SV | <input type="checkbox"/> 3562SV | <input type="checkbox"/> 3563SV |

### Flat Knit

|                                                     | 18-21 mmHg                      | 23-32 mmHg                      | 34-46 mmHg                      |
|-----------------------------------------------------|---------------------------------|---------------------------------|---------------------------------|
| <input type="checkbox"/> Juzo Strong                | <input type="checkbox"/> 3051   | <input type="checkbox"/> 3052   | <input type="checkbox"/> 3053   |
| <input type="checkbox"/> Juzo Strong Silver (Beige) | <input type="checkbox"/> 3051SV | <input type="checkbox"/> 3052SV | <input type="checkbox"/> 3053SV |
| <input type="checkbox"/> Juzo Expert                | <input type="checkbox"/> 3021   | <input type="checkbox"/> 3022   | <input type="checkbox"/> 3023   |
| <input type="checkbox"/> Juzo Expert Silver (Beige) | <input type="checkbox"/> 3021SV | <input type="checkbox"/> 3022SV | <input type="checkbox"/> 3023SV |
| <input type="checkbox"/> Juzo Expert Cotton         | <input type="checkbox"/> 3021CO | <input type="checkbox"/> 3022CO | <input type="checkbox"/> 3023CO |

## Circular Knit Styles & Accessories

☐ CG ☐ CH with shoulder cap and strap ☐ CH with shoulder cap and hook & loop to bra (Dynamic)  
☐ Beaded silicone border (CG)

## Flat Knit Styles & Accessories

### NEW Elbow Functional Zone (Expert Line)

☐ CG ☐ Beaded silicone border ☐ Slant top (Standard on Strong)  
☐ Straight top (Standard on Expert) ☐ Seam on the outside (with elbow dart)  
☐ Elbow dart (Standard Strong, typically not needed for Expert)  
☐ Silver comfort patch (placed on seam side, medial)  
☐ Smooth comfort patch (placed on seam side, medial)

### CH with shoulder cap and strap

☐ Elbow dart (typically not needed for Expert)  
☐ Silver comfort patch (placed on seam side)  
☐ Smooth comfort patch (placed on seam side)


### CH with shoulder cap and velcro to bra

☐ Elbow dart (typically not needed for Expert)  
☐ Silver comfort patch (placed on seam side)  
☐ Smooth comfort patch (placed on seam side)

## Colors (for Juzo Strong & Juzo Expert)

☐ Beige ☐ Fuchsia ☐ Blue ☐ Dark Blue ☐ Gray ☐ Chestnut ☐ Black  
☐ Violet ☐ Trend Color \_\_\_\_\_

## Left



## Right

